



Heat Shrink Male Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy
Catalog # [YHSQ18M25X03](#)

Cu Heat Shrink Male Quick Disconnect, 18-22 AWG, 1.46" L,
0.25" W, Nylon Insul, Serrated bbl, Tin plated, Red(Insul Color),
For Use On Cu Cond.



Application

For Use On Copper Conductor

General

Catalog Number	YHSQ18M25X03
Connector Type	Male Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS
UPC	781810477090

Dimensions

Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.25 in
Dimension - Pad Width inch	0.25 in
Dimension - Strip Length inch	5/16

Conductor Related

Conductor Size	22 - 18 AWG
Conductor Type	- CU C Solid-Size - CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1200
Packaging Type	Bag
Pallet Quantity	99999

Product Assets

[3D Models - YHSQ18M25X03_MODEL-PDF](#)
[3D Models - YHSQ18M25X03_MODEL-STEP](#)
[3D Models - YHSQ18M25X03_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Product Cross Section Image\(s\) - BUR_YHSQ18M25X03_LineArt](#)
[Sales Drawings - 50094213](#)



A proud member of the Hubbell Family.