



# YNS52RT, ACSR - Jumper Loop Sleeve

By Burndy  
Catalog # [YNS52RT](#)



HYSPLICE™, ACCOM: 1113 54-19 STR - 135 kcmil ACSR 1277-1280  
kcmil ACSR 1351.5-1510 kcmil AL INDEX: 728 T&B 189.

### General

|                   |                |
|-------------------|----------------|
| Catalog Number    | YNS52RT        |
| Connector Type    | Splice         |
| Die Index         | 728            |
| Material          | Aluminum       |
| Trade Name        | HYSPLICE™      |
| UPC               | 781810180631   |
| UPC 14 Digit GTIN | 00781810180631 |

### Dimensions

|                               |          |
|-------------------------------|----------|
| Dimension - Diameter Max Size | 2.25 in  |
| inch                          |          |
| Dimension - L Length Overall  | 411 mm   |
| mm                            |          |
| Dimension - Length Overall    | 16.20 in |
| inch                          |          |
| Dimension - Outside Diameter  | 2.25 in  |
| inch                          |          |

### Conductor Related

|                           |                                                                                                                                           |
|---------------------------|-------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - ACAR Str Size | 1277 KCMIL - 1280 KCMIL                                                                                                                   |
| Range                     |                                                                                                                                           |
| Conductor - ACSR Str Size | 1113 (54/19) Finch kcmil;1192.5 (45/7) Bunting kcmil;1192.5 (54/19) Grackle kcmil;1272 (54/19) Pheasant kcmil;1351.5 (54/19) Martin kcmil |

|                               |                                 |
|-------------------------------|---------------------------------|
| Conductor - ACSR Str Size     | 1113 (54/19) Finch kcmil-1351.5 |
| Range                         | (54/19) Martin kcmil            |
| Conductor - AL Str Size       | 1351.5 KCMIL - 1510 KCMIL       |
| Conductor - AL Str Size Range | 1351.5 KCMIL - 1510 KCMIL       |

### Certifications And Compliance

|                               |    |
|-------------------------------|----|
| Certification - CSA Approved  | No |
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Certification - cULus         | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| UL Listed                     | No |

### Logistics

|                 |     |
|-----------------|-----|
| Carton Quantity | 4   |
| Pallet Quantity | 384 |

### Product Assets

- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YNS-RT\\_LINEART\\_BW](#)
- [Sales Drawings - SD058033-01](#)
- [Specifications - YNS52RT Specification Sheet French](#)
- [Specifications - YNS52RT Specification Sheet English](#)



A Hubbell brand