



YPC40A36, Figure 6-shaped Connector

By Burndy
Catalog # [YPC40A36](#)



Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run, Al and Cu:600 (61) - 800 (61).

General

Catalog Number	YPC40A36
Die Index	T
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
UPC	781810138700
UPC 12 Digit	7818101387000

Dimensions

Dimension - Height inch	3.70 in
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5 in
Dimension - Width inch	1.88 in

Conductor Related

Conductor - ACSR Str Run Range	556.5 kcmil-795 kcmil
Conductor - ACSR Str Tap Range	336.4 kcmil-556.5 kcmil
Conductor - AL Str Run	600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
Conductor - AL Str Run Range	600 kcmil-800 kcmil
Conductor - AL Str Tap	397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - AL Str Tap Range	397 kcmil-600 kcmil
Conductor - Copper Str Run	600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Run Range	600 kcmil-800 kcmil
Conductor - Copper Str Tap	397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - Copper Str Tap Range	397 kcmil-600 kcmil
Conductor Type	• AL C Str-Run • CU C Str-Run • CU C Solid-Run • ACSR C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap • ACSR C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section H - Overhead Distribution](#)
[Product Cross Section Image\(s\) - BUR_YPCAU_Lineart](#)
[Sales Drawings - sd051577-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YPC40A36-SPEC-EN | REV 6/2024