

Compression Splice

By Burndy
Catalog # [YS38FXLTCKITC](#)

500 kcmil H,I,K / 550 kcmil G,H,I,535 DLO CU, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink Pink Color Code, L99 Die Index.



Application

Wire Splice

General

Catalog Number	YS38FXLTCKITC
Color Code	Pink
Color Code - Side A	Pink
Color Code - Side B	Pink
Connector Type	STANDARD BARREL KITS
Die Index	L99
Die Index Run Side	L99
Die Index Tap Side	L99
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLINK™
UPC	781810343999
UPC 12 Digit	7818103439999

Dimensions

Dimension - B Length inch	1.77 in
Dimension - L Length Overall mm	109.22 mm
Dimension - Length BB inch	1.77 in
Dimension - Length Overall inch	4.3 in
Dimension - Strip Length inch	1.77

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	535 kcmil
Conductor - Copper Flex G Size A	500 kcmil
Conductor - Copper Flex G Size B	500 kcmil
Conductor - Copper Flex G Size Range	550 kcmil
Conductor - Copper Flex H Size A	500 kcmil
Conductor - Copper Flex H Size B	500 kcmil
Conductor - Copper Flex H Size Range	500 / 550 kcmil
Conductor - Copper Flex I Size A	500 kcmil
Conductor - Copper Flex I Size B	500 kcmil
Conductor - Copper Flex I Size Range	500 / 550 kcmil
Conductor - Copper Flex K Size A	500 kcmil
Conductor - Copper Flex K Size B	500 kcmil
Conductor - Copper Flex K Size Range	500 kcmil
Conductor - Copper Flex M Size A	500 kcmil
Conductor - Copper Flex M Size B	500 kcmil
Conductor - Copper Str Size	500 Kcmil
Conductor - Copper Str Size Range	500 / 550 kcmil
Conductor - Material	COPPER
Conductor Size	500-550 KCMIL
Conductor Type	FLEX
Wire Size	500 kcmil H,I,K / 550 kcmil G,H,I,535 DLO

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed

No

Logistics

Carton Quantity

10

Pallet Quantity

900

Product Assets

[3D Models - YS38FXLTCKITC_MODEL-PDF](#)

[3D Models - YS38FXLTCKITC_MODEL-IGES](#)

[3D Models - YS38FXLTCKITC_MODEL-STEP](#)

[Catalogs - Full Line BURNDY Catalog](#)

[Catalogs - Section C - Compression Connections](#)

[Customer Notices - Prop 65 Notice](#)

[Sales Drawings - 10101349](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YS38FXLTCKITC-SPEC-EN | REV 6/2024