



YST2828, Cu Compression Tee, #4 AWG Str Run and Tap

By Burndy
Catalog # [YST2828](#)



Copper Compression Tee, 4 AWG (Str) (Run & Tap), Tin Plated.

Application

T-Connector

General

Catalog Number	YST2828
Color Code	Purple
Color Code - Side A	Purple
Color Code - Side B	Purple
Connector Type	T-COUPLER
Die Index	15/15
Die Index Run Side	15
Die Index Tap Side	15
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYTEE
Temperature Rating	194
Trade Name	HYTEE™
Type	YST, Uninsulated T
UPC	781810510001
UPC 12 Digit	7818105100011

Dimensions

Dimension - A Outside Diameter inch	0.69 in
Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.62 in
Dimension - B Outside Diameter inch	0.69 in
Dimension - Height inch	2.44 in
Dimension - L Length Overall mm	106 mm
Dimension - Length BB inch	1.75 in
Dimension - Length Overall inch	4.19 in
Dimension - Width inch	1.75 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Run	4/0 AWG
Conductor - Copper Str Run Range	4/0 AWG
Conductor - Copper Str Tap	4/0 AWG
Conductor - Copper Str Tap Range	4/0 AWG
Conductor - Material	COPPER
Conductor Size	4/0 AWG-4/0AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Pallet Quantity	7400

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YST_LineArt](#)
[Sales Drawings - 2388610](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YST2828-SPEC-EN | REV 6/2024