



Uninsulated Splice For 12 - 10 AWG

By Burndy
Catalog # [YSV10H](#)

UNINSULATED BUTT SPLICE, 600 VOLTS MAXIMUM.



General

Catalog Number	YSV10H
Connector Type	Seamless Butt Splice
Feature - Barrel Style	Shrouded
Material	Copper
Plated	Y
Plating Type	Tin
Temperature Rating	90
Trade Name	HYLINK™
Type	Splice
UPC	781810806081
UPC 12 Digit	7818108060811

Dimensions

Dimension - B Length fraction	5/16 in
Dimension - B Length inch	0.31 in
Dimension - Inside Diameter inch	0.13 in
Dimension - L Length Overall mm	27 mm
Dimension - Length Overall inch	1.06 in
Dimension - Outside Diameter inch	0.21 in
Dimension - Strip Length inch	5/16

Electrical Ratings

Voltage - Maximum	35000 V
-------------------	---------

Conductor Related

Conductor - Copper Solid Size	12;11;10
Conductor - Copper Solid Size Range	12-10
Conductor - Copper Str Aircraft Size	AN 12;AN 10
Conductor - Copper Str Aircraft Size Range	AN 12-AN 10
Conductor - Copper Str Navy Size	6 (7);6 (19);9 (7);9 (37)
Conductor - Copper Str Navy Size Range	6 (7)-9 (37)
Conductor - Copper Str Size	12;10
Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size• CU C Str Aircraft-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	500
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Product Cross Section Image\(s\) - BUR_YSV10H_LineArt](#)
[Sales Drawings - 50094199](#)





A proud member of the Hubbell Family.