



YSV14HBOX, Uninsulated Splice For 16 - 14 AWG

By Burndy
Catalog # [YSV14HBOX](#)

Uninsulated Splice For 16 - 14 AWG.

Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper dept of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

Application

For All Heavy Duty Industrial And General Purpose Applications

General

Catalog Number	YSV14HBOX
Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810534502
UPC 14 Digit GTIN	00781810534502

Dimensions

Cable Insulation Diameter Maximum	0.15 in
Dimension - Diameter Max Size inch	0.15 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.94 in



Dimension - Outside Diameter inch 0.16 in

Dimension - Strip Length inch 1/4 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - Copper Solid Size	20;18;17;16;15;14;13;12
Conductor - Copper Str Aircraft Size	AN 20;AN 18;AN 16;AN 14;AN 12
Conductor - Copper Str Size	22;20;18;16;14
Conductor Size	16 - 14 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	1200
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_KFFYSVH_LineArt](#)
[Sales Drawings - 50094199](#)
[Specifications - YSV14HBOX Specification Sheet](#)
[Specifications - YSV14HBOX Specification Sheet French](#)