



Uninsulated Splice For 1 AWG

By Burndy
Catalog # [YSVICLBOX](#)

Copper Hylink, 1, 1.46 in L, Uninsulated Butt Splice 600 Volts Maximum.



Application

For Aircraft, Light Duty Industrial And General Purpose Applications

General

Catalog Number	YSVICLBOX
Connector Type	Seamless Butt Splice
Die Index	42
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810534854

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.62 in
Dimension - L Length Overall mm	37 mm
Dimension - Length Overall inch	1.46 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Strip Length inch	5/8 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	1 AWG
Conductor - Copper Str Aircraft Size	AN 1
Conductor - Copper Str Size	1 AWG
Conductor Size	1 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size• CU C Str Aircraft-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YSV-L_LineArt](#)
[Sales Drawings - 50094198](#)



A proud member of the Hubbell Family.