



Uninsulated Splice For 4/0 AWG

By Burndy
Catalog # [YSV28L](#)

Copper Compression Splice, AN-4/0, 1.94" Splice Length, Short Barrel, Tin Plated.



Application

For Aircraft, Light Duty Industrial And General Purpose Applications

General

Connector Type	Seamless Butt Splice
Die Index	46
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810026427

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94 in
Dimension - Outside Diameter inch	0.77 in
Dimension - Strip Length inch	7/8 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	4/0 AWG
Conductor - Copper Str Aircraft Size	AN 0000
Conductor - Copper Str Size	4/0 AWG
Conductor Size	4/0 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Pallet Quantity	18500

Product Assets

[3D Models - YSV28L_MODEL-PDF](#)
[3D Models - YSV28L_MODEL-STEP](#)
[3D Models - YSV28L_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YSV-L_LineArt](#)
[Sales Drawings - 50094198](#)



A proud member of the Hubbell Family.