

YSV6CFXB, Compression Splice, #6 Str (61/24), #6 AWG

By Burndy

Catalog # [YSV6CFXB](#)



Telecom Belled Copper Hylink, #6 Str.(61/24) #6 AWG, 30 Navy, 2.62 IN L, Cable Strip Length: 1-5/16 IN.

Application

For Higher voltage applications

General

Catalog Number	YSV6CFXB
Color Code	Blue
Connector Type	Splice
Die Index	7
EU RoHS Indicator	Yes
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810041505
UPC 14 Digit GTIN	00781810041505

Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.22 in
Dimension - D inch	0.37 in
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.62 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Strip Length inch	1-5/16 in

Conductor Related

Conductor - Copper DLO Size	6 (61/#24) DLO
Conductor - Copper Flex G Size	6 AWG
Conductor - Copper Flex H Size	6 AWG
Conductor - Copper Flex I Size	6 AWG
Conductor - Copper Flex K Size	6 AWG
Conductor - Copper Flex M Size	6 AWG
Conductor - Copper Solid Size	6 AWG
Conductor - Copper Str	6
Compact Size	
Conductor - Copper Str	6
Compact Size Range	
Conductor - Copper Str Navy Size	30 (19)
Conductor - Copper Str Size	6 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE208037-01_F](#)
[Specifications - YSV6CFXB Specification Sheet English](#)
[Specifications - YSV6CFXB](#)
[Specifications - BURNDY_YSV6CFXB_Specsheet](#)