

ASA250U, Terminal Stacking Adapter, Al/Cu, 2-Slot, 250 kcmil



By Burndy
Catalog # ASA250U

Terminal Stacking Adapter, 2 Slots, 250 kcmil, Al/Cu Rated, Tin Plated.

Features

- For use on terminals made from copper or aluminum
- May be used with standard NEMA two and four hole terminals
- TO stack four hole NEMA terminations use two stacking adapters assembled side-by-side
- Only three sizes necessary to accommodate terminals from 250 kcmil through 1000 kcmil

Application

For Aluminum And Copper Terminals

General

Catalog Number	ASA250U
EU RoHS Indicator	Yes
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Plating Type	Tin
Sub Brand	HYSTACK
Temperature Rating	194° F
Trade Name	HYSTACK™
Type	Stacking Adapters
UPC	781810521007
UPC 12 Digit	7818105210077

Dimensions

Dimension - Bolt Size inch	2.75 in
Dimension - Height fraction	7/9 in
Dimension - Height inch	0.77 in
Dimension - Height mm	19.6 mm
Dimension - L Length Overall mm	20 mm
Dimension - Length Overall inch	0.78 in
Dimension - Outside Diameter inch	0.87 in

Dimension - Pad Width inch 1.00 in

Electrical Ratings

Rating - Minimum Voltage 600

Conductor Related

Conductor - AL Str Size	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - AL Str Size Range	1/0 AWG-250 kcmil
Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	1/0 -250 kcmil
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Pallet Quantity	4640

Product Assets

- [3D Models - ASA250U_MODEL-IGES](#)
- [3D Models - ASA250U_MODEL-STEP](#)
- [3D Models - ASA250U_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_ASA-U_LineArt](#)
- [Sales Drawings - sd078073-01](#)



A Hubbell brand