

ASA800U, Terminal Stacking Adapter, Al/Cu, 2-Slot, 800 kcmil

By Burndy
Catalog # ASA800U



Terminal Stacking Adapter, 2 Slots, 800 kcmil, Al/Cu Rated, Tin Plated.

Features

- For use on terminals made from copper or aluminum
- May be used with standard NEMA two and four hole terminals
- TO stack four hole NEMA terminations use two stacking adapters assembled side-by-side
- Only three sizes necessary to accommodate terminals from 250 kcmil through 1000 kcmil

Application

For Aluminum And Copper Terminals

General

Catalog Number	ASA800U
EU RoHS Indicator	Yes
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Plating Type	Tin
Sub Brand	HYSTACK
Temperature Rating	194° F
Trade Name	HYSTACK™
Type	Stacking Adapters
UPC	781810521021
UPC 12 Digit	7818105210211

Dimensions

Dimension - Bolt Size inch	3.50 in
Dimension - Height fraction	1-1/8 in
Dimension - Height inch	1.13 in
Dimension - Height mm	28.7 mm
Dimension - L Length Overall mm	20 mm
Dimension - Length Overall inch	0.78 in
Dimension - Pad Width inch	1.00 in

Electrical Ratings

Rating - Minimum Voltage 600

Conductor Related

Conductor - AL Str Size	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
Conductor - AL Str Size Range	1/0 AWG-800 kcmil
Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Size Range	1/0 -800 kcmil
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Pallet Quantity	4640

Product Assets

[3D Models - ASA800U_MODEL-PDF](#)
[3D Models - ASA800U_MODEL-STEP](#)

[3D Models - ASA800U_MODEL-IGES](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_ASA-U_LineArt](#)
[Sales Drawings - sd078073-01](#)
[Specifications - ASA800U](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY_MX-ASA800U-SPEC-EN | REV 1/2025