

## ASA800U, Terminal Stacking Adapter, Al/Cu, 2-Slot, 800 kcmil

By Burndy  
Catalog # ASA800U



Terminal Stacking Adapter, 2 Slots, 800 kcmil, Al/Cu Rated, Tin Plated.

### Features

- For use on terminals made from copper or aluminum
- May be used with standard NEMA two and four hole terminals
- TO stack four hole NEMA terminations use two stacking adapters assembled side-by-side
- Only three sizes necessary to accommodate terminals from 250 kcmil through 1000 kcmil

### Application

For Aluminum And Copper Terminals

### General

Catalog Number	ASA800U
EU RoHS Indicator	Yes
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Plating Type	Tin
Sub Brand	HYSTACK
Temperature Rating	194° F
Trade Name	HYSTACK™
Type	Stacking Adapters
UPC	781810521021
UPC 12 Digit	7818105210211

### Dimensions

Dimension - Bolt Size inch	3.50 in
Dimension - Height fraction	1-1/8 in
Dimension - Height inch	1.13 in
Dimension - Height mm	28.7 mm
Dimension - L Length Overall mm	20 mm
Dimension - Length Overall inch	0.78 in
Dimension - Pad Width inch	1.00 in

### Electrical Ratings

Rating - Minimum Voltage 600

### Conductor Related

Conductor - AL Str Size	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
Conductor - AL Str Size Range	1/0 AWG-800 kcmil
Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Size Range	1/0 -800 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	10
Pallet Quantity	4640

### Product Assets

[3D Models - ASA800U\\_MODEL-PDF](#)  
[3D Models - ASA800U\\_MODEL-STEP](#)

[3D Models - ASA800U\\_MODEL-IGES](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_ASA-U\\_LineArt](#)  
[Sales Drawings - sd078073-01](#)  
[Specifications - ASA800U](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_MX-ASA800U-SPEC-EN | REV 10/2024