



## B3G12N Flexible Copper Braid

By Burndy  
Catalog # [B3G12N](#)

Cu Flexible Braid, 2 Holes 2 Ferrules, 1.75" Spacing, 12.00" L,  
Amp Rating: 960(Indoor) 1150(Outdoor)



### General

Catalog Number	B3G12N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
Plated	Y
UPC	781810004968

### Dimensions

Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.69 in
Length	12 in

### Electrical Ratings

Rating - Indoor Amperage	960
Rating - Outdoor Amperage	1150

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_BD\\_Lineart](#)  
[Sales Drawings - SE..212210-01](#)  
[Specifications - B3G12N](#)