

BA10E8, Vinyl Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # BA10E8



Copper Terminal, Ring Tongue, 12-10 AWG, #6-#8 Stud, Vinyl Insulated, Tin Plated.

Application

For Commercial, Light Duty Industrial Control and Power Circuit Applications

General

Catalog Number	BA10E8
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810026519
UPC 12 Digit	7818100265199

Dimensions

Dimension - Bolt Size fraction	#8
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Length Overall inch	1.00 in
Dimension - Pad Width inch	0.36 in
Dimension - Stud Size inch	#8
Dimension - Z (inch)	0.26 in

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	500
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_BA16E6_LineArt](#)
[Sales Drawings - 50093722](#)
[Specifications - BA10E8](#)