



BB048L9T14 Flexible Copper Braid

By Burndy

Catalog # [BB048L9T14](#)

Flexible Copper Braid



General

Catalog Number	BB048L9T14
Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810552476
UPC 12 Digit	7818105524766

Dimensions

Dimension - L Length Overall mm	229
Dimension - Length Overall inch	9
Dimension - N inch	0.5 in
Dimension - Stud Size inch	1/4
Length	9 in

Electrical Ratings

Amperage Rating	93 A
Rating - Indoor Amperage	150
Rating - Outdoor Amperage	150

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Pallet Quantity	2250

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_B_lineart](#)
- [Sales Drawings - 50007334](#)