



BDBLHC223503, 3-Pole Power Distribution Block

By Burndy

Catalog # [BDBLHC223503](#)

Terminal block covers, AWG 6 - 350 kcmil (Run), AWG 6 - 350 kcmil (Tap), Power Distribution Block, 7.89 W, 3.55 H



Application

Industrial control feeder, HVAC system and wire ways

General

| | |
|--------------------|---------------|
| Catalog Number | BDBLHC223503 |
| EU RoHS Indicator | Yes |
| Insulation | Y |
| Material | Aluminum |
| Number Of Poles | 3 |
| Plated | Y |
| Plating Type | Tin |
| Sub Brand | VERSI-POLE |
| Temperature Rating | 194° F |
| Trade Name | VERSIPOLE™ |
| Type | BDB |
| UPC | 781810645956 |
| UPC 12 Digit | 7818106459566 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Height inch | 3.55 |
| Dimension - Height mm | 90.2 mm |
| Dimension - L Length Overall mm | 200 |
| Dimension - Length Overall inch | 7.89 |
| Dimension - Width inch | 5.70 in |
| Dimension - Width mm | 145 mm |

Electrical Ratings

| | |
|--------------------------|-------|
| Amperage Rating | 620 A |
| Rating - Minimum Voltage | 600 |

Conductor Related

| | |
|----------------------------------|---|
| Conductor - AL Str Run | 6;4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;3 |
| Conductor - AL Str Run Range | 6-350 |
| Conductor - AL Str Tap | 6;4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;3 |
| Conductor - AL Str Tap Range | 6-350 |
| Conductor - Copper Str Run | 6;5;4;3;2;1;1/0;2/0;3/0;4/0;250;300;3 |
| Conductor - Copper Str Run Range | 6-350 |
| Conductor - Copper Str Tap | 6;5;4;3;2;1;1/0;2/0;3/0;4/0;250;300;3 |
| Conductor - Copper Str Tap Range | 6-350 |
| Conductor Type | <ul style="list-style-type: none">• AL C Str-Run• CU C Str-Run• AL C Str-Tap• CU C Str-Tap |

Certifications And Compliance

| | |
|-------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance | CM |
| Status | |
| UL Listed | Yes |

Logistics

| | |
|-----------------|---|
| Carton Quantity | 6 |
|-----------------|---|

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_VERSIPOLE_Large_Lineart](#)
[Sales Drawings - 50018991](#)
[Specifications - BDBLHC223503](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-BDBLHC223503-SPEC-EN | REV 10/2024