



## BDBLHC263503, 3-Pole Power Distribution Block

By Burndy  
Catalog # [BDBLHC263503](#)

Power Distribution Block, 3 Pole, AWG 6 - 350 kcmil (Run), AWG 14 - 2/0 (Tap)



### Application

Industrial control feeder, HVAC system and wire ways

### General

Catalog Number	BDBLHC263503
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Number Of Poles	3
Plated	Y
Plating Type	Tin
Sub Brand	VERSI-POLE
Temperature Rating	194° F
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810646076
UPC 12 Digit	7818106460766

### Dimensions

Dimension - Height inch	3.55
Dimension - Height mm	90.2 mm
Dimension - L Length Overall mm	200
Dimension - Length Overall inch	7.89
Dimension - Width inch	5.70 in
Dimension - Width mm	145 mm

### Electrical Ratings

Amperage Rating	620 A
Rating - Minimum Voltage	600

### Conductor Related

Conductor - AL Str Run	6;4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;3
Conductor - AL Str Run Range	6-350
Conductor - AL Str Tap	12;10;8;6;4;3;2;1/0;2/0
Conductor - AL Str Tap Range	14-2/0
Conductor - Copper Str Run	6;5;4;3;2;1;1/0;2/0;3/0;4/0;250;300;3
Conductor - Copper Str Run Range	6-350
Conductor - Copper Str Tap	14;12;10;9;8;7;6;5;4;3;2;1/0;2/0
Conductor - Copper Str Tap Range	14-2/0
Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Run</li><li>• CU C Str-Run</li><li>• AL C Str-Tap</li><li>• CU C Str-Tap</li></ul>

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	6
-----------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_VERSIPOLE\\_Large\\_Lineart](#)  
[Sales Drawings - 50018991](#)  
[Specifications - BDBLHC263503](#)

