

## BDBMHC262/01, 1-Pole Power Distribution Block

By Burndy  
Catalog # BDBMHC262/01



POWER DISTRIBUTION BLOCKS, 1 POLE 600V AL9CU, RUN (2)  
#14-2/0 AWG TAP:(6) #14-#2

### General

Catalog Number	BDBMHC262/01
Construction Material - Main	HIGHLY CONDUCTIVE TIN-PLATED ALUMINUM
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Number Of Poles	1
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	POWER DISTRIBUTION BLOCK
UPC	781810646021
UPC 12 Digit	7818106460211

### Dimensions

Dimension - Height inch	3.25 in
Dimension - Height mm	82.6 mm
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5.00 in
Dimension - Width inch	1.85 in
Dimension - Width mm	47 mm
Dimensions	5 in x 1.85 in x 3.25 in
Height	3.25 in
Length	5 in
Width	1.85 in

### Electrical Ratings

Amperage Rating	350 A
Rating - Minimum Voltage	600
Voltage Rating	600 V

### Conductor Related

Conductor - AL Str Run	12;10;8;6;4;3;2;1;1/0;2/0
Conductor - AL Str Run Range	12-2/0
Conductor - AL Str Tap	12;10;8;6;4;3;2
Conductor - AL Str Tap Range	12-2
Conductor - Copper Str Run	14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0
Conductor - Copper Str Run Range	14-2/0
Conductor - Copper Str Tap	14;12;10;9;8;7;6;5;4;3;2
Conductor - Copper Str Tap Range	14-2
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• AL C Str-Tap</li> <li>• CU C Str-Tap</li> </ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	18
-----------------	----

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_VERSIPOLE\\_Medium\\_Lineart](#)  
[Sales Drawings - 50018989](#)  
[Specifications - BURNDY\\_BDBMHC26201\\_Specsheet](#)  
[Specifications - BDBMHC262/01](#)