



BGBL4, Aluminum Lay-in Lug, 4-14 AWG, 1/4" Stud, Tin Plated

By Burndy
Catalog # [BGBL4](#)

Aluminum Lay-in Lug, 4-14 AWG, 1/4" Stud, Tin Plated.



Features

- UL486B Listed, AL9CU Rated for copper and aluminum conductor combinations up to 90°C, 600 Volt applications
- UL Recognized for grounding and bonding
- Lay-in feature eases installation

Application

For Copper And Aluminum Conductor Combinations Up To 90 DEG C, 600 Volt Applications

General

Catalog Number	BGBL4
EU RoHS Indicator	Yes
Hex Size	Slot
Installation Torque	35 LBS/in
Recommended in-lb	
Material	Aluminum
Material Type - Screw	Steel - Zinc Plated
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin
Sub Brand	QIKLUG
Temperature Rating	194
Trade Name	QIKLUG™
Type	BGBL, Lay-In
UPC	781810124857
UPC 12 Digit	7818101248577

Dimensions

Dimension - D inch	0.62 in
Dimension - Height fraction	7/9 in
Dimension - Height inch	0.78 in
Dimension - Height mm	19.8 mm
Dimension - Hole Size inch	0.22 in
Dimension - Hole Size mm	6 mm
Dimension - L Length Overall mm	27 mm
Dimension - Length Overall inch	1.07 in
Dimension - N inch	0.19 in
Dimension - Pad Width inch	0.38 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG
Conductor - AL Str Size Range	8 AWG-4 AWG
Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	14 AWG-4 AWG
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size• CU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-B
Standards - Industry Standards Met	UL 486A-B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity 2400

Product Assets

[3D Models - BGBL4_MODEL-PDF](#)
[3D Models - BGBL4_MODEL-STEP](#)
[3D Models - BGBL4_MODEL-IGES](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_BGBL_LineArt](#)
[Sales Drawings - SE..212385-01](#)
[Specifications - BGBL4](#)

