

BGBL4, Aluminum Lay-in Lug, 4-14 AWG, 1/4" Stud, Tin Plated



By Burndy
Catalog # BGBL4

Aluminum Lay-in Lug, 4-14 AWG, 1/4" Stud, Tin Plated.

Features

- UL486B Listed, AL9CU Rated for copper and aluminum conductor combinations up to 90°C
- UL Recognized for grounding and bonding
- Lay-in feature eases installation

Application

For Copper And Aluminum Conductor Combinations Up To 90 DEG C

General

Catalog Number	BGBL4
EU RoHS Indicator	Yes
Hex Size	Slot
Installation Torque	35 LBS/in
Recommended in-lb	
Material	Aluminum
Material Type - Screw	Steel - Zinc Plated
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin
Sub Brand	QIKLUG
Temperature Rating	194
Trade Name	QIKLUG™
Type	BGBL, Lay-In
UPC	781810124857
UPC 12 Digit	7818101248577

Dimensions

Dimension - D inch	0.62 in
Dimension - Height fraction	7/9 in
Dimension - Height inch	0.78 in
Dimension - Height mm	19.8 mm
Dimension - Hole Size inch	0.22 in
Dimension - Hole Size mm	6 mm
Dimension - L Length Overall mm	27 mm
Dimension - Length Overall inch	1.07 in
Dimension - N inch	0.19 in
Dimension - Pad Width inch	0.38 in

Electrical Ratings

Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG
Conductor - AL Str Size Range	8 AWG-4 AWG
Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	14 AWG-4 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size • CU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-B
Standards - Industry Standards	UL 486A-B
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	2400
-----------------	------

Product Assets

[3D Models - BGBL4_MODEL-PDF](#)
[3D Models - BGBL4_MODEL-STEP](#)
[3D Models - BGBL4_MODEL-IGES](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_BGBL_LineArt](#)
[Sales Drawings - SE..212385-01](#)
[Specifications - BGBL4](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY_MX-BGGL4-SPEC-EN | REV 1/2025