

BIBS3506DB, Direct Burial Submersible Six Conductor Insulated Multi-Tap Connector

By Burndy
Catalog # [BIBS3506DB](#)



Direct Burial UNITAP™, 350 Kcmil -12 AWG Str., 7.45 in L, Designed specifically for direct burial applications.

Features

- Supplied with aluminum set-screws
- Supplied with oxide inhibitor pre-installed
- Submersible rated and suitable for Direct Burial

Application

For Outside Direct Burial

General

| | |
|---------------------|----------------------------------|
| Catalog Number | BIBS3506DB |
| Connector Type | Multi Tap |
| EU RoHS Indicator | Yes |
| Installation Torque | 450 LBS/in |
| Recommended in-lb | |
| Insulation | Y |
| Material | Aluminum |
| Number Of Ports | 6 |
| Plated | N |
| Plating Type | Unplated |
| Sub Brand | UNITAP |
| Temperature Rating | 194 |
| Trade Name | UNITAP™ |
| Type | BIBS, Multi-Port - Direct Burial |
| UPC | 781810523629 |
| UPC 12 Digit | 7818105236299 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Height inch | 2.46 in |
| Dimension - L Length Overall mm | 189 mm |
| Dimension - Length Overall inch | 7.45 in |
| Dimension - Strip Length inch | 1.125 |
| Dimension - Width inch | 4.06 in |
| Dimension - Width mm | 103 mm |

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

| | |
|-----------------------------------|--|
| Conductor - AL Str Size Range | 12 - 350 Str |
| Conductor - Copper Str Size Range | 12 - 350 Str |
| Conductor Size | 12 AWG-350 KCMIL |
| Conductor Type | <ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size |

Certifications And Compliance

| | |
|---|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance | CM |
| Status | |
| UL Listed | Yes |

Product Assets

- [3D Models - BIBS3506DB_MODEL-PDF](#)
- [3D Models - BIBS3506DB_MODEL-STEP](#)
- [3D Models - BIBS3506DB_MODEL-IGES](#)
- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BIBS_Lineart](#)
- [Sales Drawings - 30013013](#)



A Hubbell brand