



BSD2050N, Static Discharge Reel, Heavy Duty, Cable Length: 50' (Nylon Covered)

By Burndy
Catalog # BSD2050N

Static Discharge Reels, Heavy Duty, Cable Length: 50 Feet
(Nylon Covered), Weight: 12 LB.



Features

- 50 foot cable length
- Automatic E-Z PULL Rewinding
- Rugged Steel Construction
- Compact Enclosed Design
- Positive Ratchet Lock with Ratchet On/Off Switch
- Steel Cable Installed
- 100 Amp Universal Jaw-Type GroundingClamp
- Red Baked-on Finish

Application

Used to dissipate static charge build-up developed while filling or dispensing fuel or other combustible liquids from fuel trucks or rail cars

General

Cable Length	50 ft
Cable Lock	Y
Cable Type	Aircraft Steel
Catalog Number	BSD2050N
Color - Housing	Red
EU RoHS Indicator	Contact Manufacturer
Material	Copper
Material Type - Outer Shell	Nylon
Physical Attribute - Number of Clamping Elements	1
Plated	N
Plating Type	Unplated
Sub Brand	REEL
Tension	Adjustable
Type	Static Discharge Reel
UPC	781810504475
UPC 12 Digit	7818105044755

Dimensions

Cable Length Active	600
Dimension - Height inch	8.8 in
Dimension - L Length Overall mm	219 mm
Dimension - Length Overall inch	8.6 in
Dimension - Width inch	3.40 in
Dimension - Width mm	86 mm

Conductor Related

Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size
----------------	---

Certifications And Compliance

Certification - CSA Approved No

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section E2 - Mechanical Grounding](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_BSD2050_LineArt](#)
[Sales Drawings - 30003968](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-BSD2050N-SPEC-EN | REV 6/2024