



C4, Cast Bronze Ground Clamp, Cable to Water Pipe or Tube

By Burndy
Catalog # C4

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper
Tube, 10 - 2 AWG, 2-1/2" - 4" Water Pipe.



Application

For Bare Wire, Connecting Grounding Conductor To Water Pipe Or Copper Tube

General

Catalog Number	C4
EU RoHS Indicator	Yes
Material	Bronze Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	CLAMP
Trade Name	N
Type	Ground Clamp
UPC	781810142325
UPC 12 Digit	7818101423255

Dimensions

Dimension - Height inch	4.13 in
Dimension - Hole Size inch	0.31 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	159 mm
Dimension - Length Overall inch	6.25 in
Dimension - Pad Width inch	1.88 in
Dimension - Thread Size	-
Dimension - Width inch	0.96 in
Dimension - Width mm	24 mm

Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	10 AWG-2 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	10 AWG-2 AWG
Conductor - Pipe EMT Size	2 1/2 in;3 in;3 1/2 in;4 in
Conductor - Pipe EMT Size Range	2 1/2 in-4 in
Conductor - Rebar Size Range	N/A

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	N
Certification - UL Recognized	N
Certification - cULus	N
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Product Assets

[3D Models - C4_MODEL-PDF](#)
[3D Models - C4_MODEL-STEP](#)
[3D Models - C4_MODEL-IGES](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CN_LineArt](#)
[Sales Drawings - 10087199](#)
[Specifications - C4](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-C4-SPEC-EN | REV 8/2024