



CT120200D0, Cable Tie, 120 Lb Tensile, Black

By Burndy
Catalog # [CT120200D0](#)



Nylon UNIRAP - 120 Lb. Tensile Strength

General

Catalog Number	CT120200D0
Color	Black
Material	NYLON 6/6
Operating Temperature Celcius	85 °C
Max	
Operating Temperature Celcius	-40 °C
Min	
Rating - Minimum Tensile Strength lbs	120
Trade Name	UNIRAP™
UPC	781810333457

Dimensions

Dimension - Bundle Diameter	2
Max inch	
Dimension - L Length Overall	221 mm
mm	
Dimension - Length Overall	8.70 in
inch	
Dimension - Width inch	0.3 in
Dimension - Width mm	8 mm

Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	3000
Packaging Type	Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT120200D0](#)