



CT120300D0, Cable Tie, 120 Lb Tensile, Black

By Burndy
Catalog # [CT120300D0](#)



Nylon UNIRAP - 120 Lb. Tensile Strength.

Features

- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

General

Catalog Number	CT120300D0
Color	Black
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	120
Trade Name	UNIRAP™
UPC	781810333471

Dimensions

Dimension - Bundle Diameter Max inch	3
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12 in

Dimension - Width inch	0.3 in
Dimension - Width mm	8 mm

Certifications And Compliance

Certification - 94V0 Rated	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	2000
Packaging Type	Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT120300D0](#)