



CT1751100Q0, Cable Tie, 11" Max Bundle, 175 Lb Tensile, UV Black

By Burndy
Catalog # [CT1751100Q0](#)



UV Black Nylon 6/6 Cable Tie, 11" Max. Bundle Dia, 175 Lbs, 36" Long, 0.35" Wide.

Features

- Cable Ties for General Use
- Most sizes available in Natural or Black
- One-piece injection molded

Application

For Outdoor Applications

General

Catalog Number	CT1751100Q0
Color	UV Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	0 °C
Rating - Minimum Tensile Strength lbs	175
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Heavy
Trade Name	UNIRAP™
Type	Heavy
UPC	781810334133

Dimensions

Dimension - Bundle Diameter Max inch	11
--------------------------------------	----

Dimension - L Length Overall mm	927 mm
Dimension - Length Overall inch	36.50 in
Dimension - Width inch	0.34 in
Dimension - Width mm	8.6 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	Yes
Certification - cULus	No
Military Spec Number	MS3367-13-0
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500
-----------------	-----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT1751100Q0](#)