



## CT18200C, Cable Tie, 2" Max Bundle, 18 Lb Tensile, Natural

By Burndy  
Catalog # [CT18200C](#)



Nylon cable ties, Tensile strength-18 Lbs, Color- Natural, 8.18"L, 0.09"W, 2.10" Bundle Dia.

### Features

- Cable Ties for General Use
- Most sizes available in Natural or Black
- One-piece injection molded

### General

Catalog Number	CT18200C
Color	Natural
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	18
Tool Type	Mini
Trade Name	UNIRAP™
UPC	781810331569

### Dimensions

Dimension - Bundle Diameter Max inch	2.10 in
Dimension - L Length Overall mm	208 mm
Dimension - Length Overall inch	8.18 in

Dimension - Width inch	0.09 in
Dimension - Width mm	2 mm

### Certifications And Compliance

Certification - 94V0 Rated	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	10000
Packaging Type	Bag

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT18200C](#)