



# CT40200CO, Cable Tie, 2" Max Bundle, 40 Lb Tensile, UV Black

By Burndy  
Catalog # [CT40200CO](#)



UV Black Nylon 6/6 Cable Tie, 2" Max. Bundle Dia, 40 Lbs, 8.50" Long, 0.15" Wide.

## Application

For Outdoor Applications

## General

Catalog Number	CT40200CO
Color	UV Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	40
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Intermediate
Trade Name	UNIRAP™
Type	Intermediate
UPC	781810332382

## Dimensions

Dimension - Bundle Diameter Max inch	2
Dimension - L Length Overall mm	225 mm
Dimension - Length Overall inch	8.87 in
Dimension - Width inch	0.14 in
Dimension - Width mm	4 mm

## Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	10000
-----------------	-------

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 50080813](#)