



CTB075RA4M, Cable Tie Mounting Base, Rubber Adhesive, Natural

By Burndy

Catalog # [CTB075RA4M](#)

Nylon Cable tie mounting bases, Color:Natural, 0.75" L, 0.75" W, Max Tie Slot Width: 0.20", Tensile Strength: 9 Lbs

General

Catalog Number	CTB075RA4M
Color	Natural
Material	NYLON 6/6
Mounting Method	Rubber adhesive or #4 screw
Operating Temperature Celcius Max	70 °C
Operating Temperature Celcius Min	0 °C
Trade Name	UNIRAP™
Type	Cable Tie Bases
UPC	781810335826

Dimensions

Dimension - B Length inch	0.74 in
Dimension - Width inch	0.74 in

Certifications And Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1000
Packaging Type	Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CTB_MOUNTING_BASE_LineArt](#)
- [Sales Drawings - 50080810](#)
- [Specifications - CTB075RA4M](#)



A Hubbell brand