

# CZ11, Grounding Clamp, Cable to Water Pipe

By Burndy  
Catalog # CZ11



Grounding Clamp, Cable to Water Pipe, 10 - 2 AWG, 1/2" - 1" Water Pipe, W/ zinc plated screws.

## Features

Die Cast Zinc with Zinc-plated steel hardware

## Application

For Bare Wire

## General

Catalog Number	CZ11
EU RoHS Indicator	Yes
Material	Zinc, Cast
Material - Hardware	Zinc Plated Steel
Plated	N
Plating Type	Zinc
Sub Brand	DIE CAST CLAMPS
Type	Grounding Mechanical
UPC	781810142387
UPC 12 Digit	7818101423877

## Dimensions

Dimension - Height inch	1.56 in
Dimension - Height mm	40 mm
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.25 in
Dimension - Pad Width inch	0.50 in
Dimension - Width inch	0.63 in
Dimension - Width mm	16 mm

## Conductor Related

Conductor - AL Str Size Range	8-2
Conductor - Armored Cable Size	N

Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	10 AWG - 2 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 in-1 in
Conductor - Rigid Pipe Size Range	1/2" - 1"

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Product Assets

- [3D Models - CZ11\\_MODEL-PDF](#)
- [3D Models - CZ11\\_MODEL-IGES](#)
- [3D Models - CZ11\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CZ11\\_LineArt](#)
- [Sales Drawings - sc210660-01](#)
- [Specifications - CZ11](#)