

## ES25R25R, Insulated AL Service Entrance Compression Sleeve

By Burndy  
Catalog # [ES25R25R](#)



Insulated AL service entrance compression sleeve for combinations of insulated CU, AL and ACSR conductors, Color Code: Yellow (Side A), Yellow (Side B).

### Features

- Pre-insulated service entrance compression connector
- Polyethylene caps prevent dirt from accumulating in barrel, grip cable for easy two-hand installation, seal out moisture
- Connector is anchored to jacket assuring the connector is under the die when crimping
- Prefilled with joint compound and stripsealed to limit oxidation and increase life of the connection

### Application

For Insulated Combinations Of Copper, Aluminum, ACSR Compressed Conductors And In Overhead Distribution

### General

Catalog Number	ES25R25R
Color Code - Side A	Yellow
Color Code - Side B	Yellow
Die Index	BG or 5/8
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	INSULINK
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810149300
UPC 12 Digit	7818101493000

### Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

### Conductor Related

Conductor - ACSR Str Size A	1 (6/1) Robin AWG;1/0 (6/1) Raven AWG
Conductor - ACSR Str Size A Range	1 (6/1) Robin AWG-1/0 (6/1) Raven AWG
Conductor - ACSR Str Size B	1 (6/1) Robin AWG;1/0 (6/1) Raven AWG
Conductor - ACSR Str Size B Range	1 (6/1) Robin AWG-1/0 (6/1) Raven AWG
Conductor - AL Str Size A	1/0 AWG;1 AWG (19 Str.)
Conductor - AL Str Size A Range	1/0 AWG-1 AWG (19 Str.)
Conductor - AL Str Size B	1/0 AWG;1 AWG (19 Str.)
Conductor - AL Str Size B Range	1/0 AWG-1 AWG (19 Str.)
Conductor - Copper Str Size A	1/0 AWG;1 AWG (19 Str.)
Conductor - Copper Str Size A Range	1/0 AWG-1 AWG (19 Str.)
Conductor - Copper Str Size B	1/0 AWG
Conductor - Copper Str Size B Range	1/0 AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	100
Pallet Quantity	24000

### Product Assets

[3D Models - ES25R25R\\_MODEL-PDF](#)  
[3D Models - ES25R25R\\_MODEL-STEP](#)  
[3D Models - ES25R25R\\_MODEL-IGES](#)  
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)

