

FL1025X03D, Uninsulated Flag-Style Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy
Catalog # [FL1025X03D](#)



Brass Flag Style Female Quick Disconnect, 12-10 AWG, Tin Plated.

Features

- Flag-style female quick disconnects provide quick, reliable, snap-together interconnections without the use of tools
- Side entrance chamfer permits connections of 90° without bending the wire

Application

Female Disconnect

General

Catalog Number	FL1025X03D
Connector Type	Flag Female Quick Disconnect
EU RoHS Indicator	Yes
Material	Brass
Plated	Y
Plating Type	Nickel
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293638

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - Length Overall inch	0.63 in
Dimension - Outside Diameter inch	0.23 in
Dimension - Strip Length inch	3/8 in

Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	600
Pallet Quantity	99999

Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_FL1025X03D_LineArt](#)
- [Sales Drawings - sd214278](#)
- [Specifications - FL1025X03D](#)