

GAR1926, Mechanical Grounding Connector, Cable to Rod or Pipe

By Burndy
Catalog # [GAR1926](#)

Mechanical Grounding Connector, Cable to Rod or Pipe, 4 AWG (Sol)-2/0 AWG (Str), 2-1/2" Pipe, 2-1/2"-2-7/8"Rod, Bright Dipped.



Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Application

For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Direct Burial Cable, Fence Post

General

Catalog Number	GAR1926
EU RoHS Indicator	Yes
Installation Torque	240 Lb-in
Recommended Run in-lb	
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Bright Dipped
Sub Brand	MECHANICAL CONNECTOR
Type	GAR
U Bolt Type	266
UPC	781810235805
UPC 12 Digit	7818102358055

Dimensions

Dimension - B Length inch	3.25 in
Dimension - Height fraction	5 in
Dimension - Height inch	5.00 in
Dimension - Height mm	127 mm
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.56 in
Dimension - Outside Diameter inch	2.88 in
Dimension - Width fraction	4-1/4 in
Dimension - Width inch	4.19 in
Dimension - Width mm	106 mm

Conductor Related

Conductor - Copper Solid Size	4 AWG
Conductor - Copper Solid Size Range	4 AWG-3/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	5 AWG-2/0 AWG
Conductor - Copper Tube Std Size	2 1/2 IPS IPS
Conductor - Copper Tube Std Size Range	2 1/2 IPS IPS
Conductor - Pipe or Round Tube Size Range	2-1/2 in
Conductor - Rod Size	2.5 in-2.88 in
Conductor - Rod Size Range	2 1/2 in-2 7/8 in
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Product Assets

[3D Models - GAR1926_MODEL-STEP](#)
[3D Models - GAR1926_MODEL-IGES](#)
[3D Models - GAR1926_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_GAR_Lineart](#)

