




GAR3907, Mechanical Grounding Connector, Conductor to Water Pipe

By Burndy
Catalog # [GAR3907](#)

Mechanical Grounding Connector, Conductor to Water Pipe, 4-4/0 AWG, 8" Pipe, 3/8" Stud.



Application

For Connecting A Small To Medium Range Copper Ground Conductor To Water Pipe As Well As Structural And Reinforcing Rod Shapes, Direct Burial Cables

General

Catalog Number	GAR3907
EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	200 lb-in
Material	Copper Alloy
Material - Hardware Plated	Galvanized Steel N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GAR3902
U Bolt Type	1028G
UPC	781810234068
UPC 12 Digit	7818102340688

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Height inch	10.00 in
Dimension - Length Overall inch	1.75 in
Dimension - Outside Diameter inch	8.62 in
Dimension - Width inch	10.62 in
Dimension - Width mm	270 mm

Conductor Related

Conductor - Copper Solid Size Range	4 AWG - 4/0 AWG
Conductor - Copper Str Size	4;3;2;1;1/0;2/0;3/0;4/0
Conductor - Copper Str Size Range	4-4/0
Conductor - Copper Tube Std Size	8
Conductor - Copper Tube Std Size Range	8
Conductor - Pipe or Round Tube Size	8 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

[3D Models - GAR3907_MODEL-STEP](#)
[3D Models - GAR3907_MODEL-IGES](#)
[3D Models - GAR3907_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section E2 - Mechanical Grounding](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_GAR3900_Lineart](#)
[Sales Drawings - SD206499-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-GAR3907-SPEC-EN | REV 6/2024