

GAR3909BU, Mechanical Grounding Connector, Conductor to Water Pipe

By Burndy
Catalog # [GAR3909BU](#)



Mechanical Grounding Connector, Conductor to Water Pipe, 4-4/0 AWG, 12" Pipe, 3/8" Stud. Silicon bronze hardware.

Features

- Cable clamp swivels at 90°
- One-wrench installation for simplified installation
- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets

General

Catalog Number	GAR3909BU
Installation Torque	200 lb-in
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	1030
UPC	781810001561
UPC 12 Digit	7818100015611

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Height inch	14.00 in
Dimension - Height mm	355.6 mm
Dimension - Length Overall inch	1.75 in
Dimension - Outside Diameter inch	12.75 in
Dimension - Width inch	14.75 in
Dimension - Width mm	375 mm

Conductor Related

Conductor - Copper Solid Size Range	4 AWG - 4/0 AWG
Conductor - Copper Str Size Range	4;3;2;1;1/0;2/0;3/0;4/0
Conductor - Copper Str Size Range	4-4/0
Conductor - Copper Tube Std Size	12
Conductor - Copper Tube Std Size Range	12
Conductor - Pipe or Round Tube Size	12 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_GARBU_Lineart](#)
- [Sales Drawings - sd206396](#)
- [Specifications - GAR3909BU](#)