

# GD2026, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy  
Catalog # [GD2026](#)



Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 4 AWG ( Sol.) - 2/0 AWG (Str.), 3" to 3-1/2" Rod, 3" Pipe.

## Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

## Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete

## General

Catalog Number	GD2026
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GD
U Bolt Type	258
UPC	781810260388
UPC 12 Digit	7818102603888

## Dimensions

Dimension - B Length inch	1.50 in
Dimension - Height fraction	5-5/8 in
Dimension - Height inch	5.63 in
Dimension - Height mm	143 mm
Dimension - Width fraction	4-7/8 in
Dimension - Width inch	4.81 in
Dimension - Width mm	122 mm

## Conductor Related

Conductor - Copper Solid Size	4;3;2;1;1/0;2/0
Conductor - Copper Solid Size Range	4-2/0

Conductor - Copper Str Size	4;3;2;1;1/0;2/0
Conductor - Copper Str Size B Range	3
Conductor - Copper Str Size Range	4-2/0
Conductor - Copper Tube Std Size	3
Conductor - Copper Tube Std Size Range	3
Conductor - Rod Size	3 in
Conductor - Rod Size Range	3 in

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Product Assets

- [3D Models - GD2026\\_MODEL-PDF](#)
- [3D Models - GD2026\\_MODEL-IGES](#)
- [3D Models - GD2026\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_gdla](#)
- [Sales Drawings - SD..013775-01](#)
- [Specifications - GD2026](#)
- [Specifications - BURNDY\\_GD2026\\_Specsheet](#)