

# GG161, Mechanical Grounding Connector, Copper Bar, Strap, Braid, or Cable to Rod or Tube

By Burndy  
Catalog # GG161



Mechanical Grounding Connector, Copper  
Bar/Strap/Braid/Cable to Rod/Tube, 1-1/4" Pipe, 1-3/8"-1-1/2"  
Rod.

## Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth or concrete
- UL467 Listed
- One wrench installation
- Type GG connector is particularly effective for use with braid for ground rods, switch handles, fence posts and gates

## Application

For Joining Copper Bar, Strap, Braid Or Cable To Rod Or Tube, Direct Burial Cables

## General

Catalog Number	GG161
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GG
U Bolt Type	204
UPC	781810260050
UPC 12 Digit	7818102600500

## Dimensions

Dimension - B Length inch	1.38 in
Dimension - Height fraction	3-1/2 in

Dimension - Height inch	3.50 in
Dimension - Height mm	88.9 mm
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

## Conductor Related

Conductor - Copper Tube Std Size	1-1/2
Conductor - Rod Size	1 1/2 in

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_GG\\_LineArt](#)  
[Sales Drawings - sd013776-01](#)  
[Specifications - GG161](#)