



## GSTUD34HY Structural Steel Ground Stud

By Burndy  
Catalog # [GSTUD34HY](#)

Structural Steel Grounding Connector; Accommodates: 4/0 AWG; 3/4" Rod; Copper Coated; Nickel Plated



### Application

- For Compression Connectors And Mechanical Connectors

### General

Catalog Number	GSTUD34HY
EU RoHS Indicator	Yes
Material	Steel
Plated	Y
Plating Type	Nickel
Sub Brand	HYGROUND, VERSITAIL
Trade Name	VERSITAIL™
Type	<ul style="list-style-type: none"><li>GSTUD-HY</li><li>GSTUD-HY</li></ul>
UPC	781810220900
UPC 12 Digit	7818102209000

### Dimensions

Dimension - B Length fraction	19/25 in
Dimension - B Length inch	0.76 in
Dimension - D inch	1.25 in
Dimension - Ground Rod Size	3/4 in
Dimension - L Length Overall mm	148 mm
Dimension - Length Overall inch	5.81 in
Physical Attribute - Tongue Angle	45 Degree

### Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Rod Size	3/4 in
Conductor - Rod Size Range	3/4 in
Conductor Type	<ul style="list-style-type: none"><li>Rod-Size</li><li>CU C Str-Size</li></ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	5
Pallet Quantity	1960

### Product Assets

- [3D Models - GSTUD34HY\\_MODEL-PDF](#)
- [3D Models - GSTUD34HY\\_MODEL-IGES](#)
- [3D Models - GSTUD34HY\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_GSTU-HY\\_LineArt](#)
- [Sales Drawings - sd..086414-01](#)



A Hubbell brand