

GSTUD38HY Structural Steel Ground Stud

By Burndy
Catalog # [GSTUD38HY](#)

Structural Steel Grounding Connector; Accommodates: #3 AWG;
3/8" Rod; Copper Coated; Nickel Plated



Application

- For Compression Connectors And Mechanical Connectors

General

Catalog Number	GSTUD38HY
EU RoHS Indicator	Yes
Material	Steel
Plated	Y
Plating Type	Nickel
Sub Brand	HYGROUND, VERSITAIL
Trade Name	VERSITAIL™
Type	GSTUD-HY
UPC	781810220887
UPC 12 Digit	7818102208877

Dimensions

Dimension - B Length fraction	16/41 in
Dimension - B Length inch	0.39 in
Dimension - D inch	1.25 in
Dimension - Ground Rod Size	3/8 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	148 mm
Dimension - Length Overall inch	5.81 in
Physical Attribute - Tongue Angle	45 Degree

Conductor Related

Conductor - Copper Str Size	3 AWG
-----------------------------	-------

Conductor - Copper Str Size Range	3 AWG
Conductor - Rod Size	3/8 in
Conductor - Rod Size Range	3/8 in
Conductor Type	<ul style="list-style-type: none"> Rod-Size CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Pallet Quantity	3920

Product Assets

- [Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_GSTU-HY_LineArt](#)
- [Sales Drawings - sd..086414-01](#)
- [Specifications - GSTUD38HY](#)