



# HSB150H48PF5, Cross-Linked Polyolefin Heat Shrinkable Heavy Wall Tube, 2/0 AWG - 350 kcmil, 1000 V, Shrink Ratio: 3 : 1.



By Burndy  
Catalog # [HSB150H48PF5](#)

Cross-Linked Polyolefin Heat Shrinkable Heavy Wall Tube, 2/0 AWG - 350 kcmil, 600 V, Shrink Ratio: 3 : 1.

### Application

For Direct Burial

### General

Catalog Number	HSB150H48PF5
Connector Type	HEAVY WALL TUBES
EU RoHS Indicator	Contact Manufacturer
Material	Cross-linked Polyolefin
Sub Brand	HEAT SHRINK
Type	HS-H-PF, Heavy Wall, Flame Retardant
UPC	781810214916

### Conductor Related

Conductor Range	#2/0 AWG - 350 Kcmil
Conductor Size	2/0AWG - 350kcmil

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	5
Number of Pieces in Package	5

### Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSB35H6PF25\\_LineArt](#)
- [Sales Drawings - SD211942-01](#)
- [Specifications - HSB150H48PF5](#)
- [Video - Heat Shrink Product Overview & Installation](#)