



HSB34H48PF5, Heat Shrink Tubing, 0.75" ID Min.(Exp.), 0.22" ID Max. (Rec.), 6-2 AWG, Heavy Wall, Black, 4" Length



By Burndy
Catalog # [HSB34H48PF5](#)

Heat Shrink Tubing, 0.75" ID Min.(Exp.), 0.22" ID Max.(Rec.), 6-2 AWG, Cross Linked Polyolefin, Heavy Wall, Flame Retardant, Black, 600V,4" Length.

Application

For Direct Burial

General

Catalog Number	HSB34H48PF5
Connector Type	HEAVY WALL TUBES
EU RoHS Indicator	Yes
Material	Cross-linked Polyolefin
Sub Brand	HEAT SHRINK
Type	HS-H-PF, Heavy Wall, Flame Retardant
UPC	781810214893

Conductor Related

Conductor Range	#6 AWG to #2 AWG
Conductor Size	6AWG - 2AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	5
Number of Pieces in Package	5

Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB35H6PF25_LineArt](#)
- [Sales Drawings - SD211942-01](#)
- [Specifications - HSB34H48PF5](#)
- [Video - Heat Shrink Product Overview & Installation](#)