



# HSC14FR, Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.125" ID Max.(Rec.), 12-10 Flex, PVC, Flame Retardant, Clear, 600V.



By Burndy  
Catalog # [HSC14FR](#)

Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.125" ID Max.(Rec.), 12-10 Flex, PVC, Flame Retardant, Clear, 600V.

## Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

## Application

For Terminations And Splices

## General

Catalog Number	HSC14FR
Color	Clear
Connector Type	CLEAR TUBES
EU RoHS Indicator	Yes
Material	Polyvinyl chloride
Sub Brand	VISISHRINK
Trade Name	VISI-SHRINK™
Type	HSC-FR, Thin Wall, Flexible, Fire Retardant
UPC	781810266199

## Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12AWG -8AWG

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSC100FR\\_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSC14FR](#)
- [Video - Heat Shrink Product Overview & Installation](#)