



HSC34FR, Vinyl Fire Retardant Clear Heat Shrink Tubing, 1/0-3/0(Code) #2-1/0(Flex), 600V.



By Burndy
Catalog # [HSC34FR](#)

Vinyl Fire Retardant Clear Heat Shrink Tubing, 1/0-3/0(Code) #2-1/0(Flex), 600V.

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Application

For Terminations And Splices

General

Catalog Number	HSC34FR
Color	Clear
Connector Type	CLEAR TUBES
EU RoHS Indicator	Yes
Material	Polyvinyl chloride
Sub Brand	VISISHRINK
Trade Name	VISI-SHRINK™
Type	HSC-FR, Thin Wall, Flexible, Fire Retardant
UPC	781810266250

Conductor Related

Conductor Range	#2 AWG to # 1/0 AWG
Conductor Size	1/0AWG - 3/0AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Product Assets

- [3D Models - HSC34FR-RECOVERY_MODEL-STEP](#)
- [3D Models - HSC34FR-RECOVERY_MODEL-IGES](#)
- [3D Models - HSC34FR-RECOVERY_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSC34FR](#)