

# K11A30U, Two Conductor Stacked Aluminum Panel Board Set Screw Connector

By Burndy  
Catalog # K11A30U



Aluminum Universal Terminal, 1 Hole, Two: 6 AWG (Str)-300 kcmil, 5/16" Stud, 2 Screws, Al/Cu Rated, Tin Plated.

## Features

- Constructed from high strength, extruded aluminum alloy
- Electro tin-plated to provide low contact resistance

## Application

For Aluminum And Copper Conductors

## General

Catalog Number	K11A30U
Connector Type	Stacked
EU RoHS Indicator	Yes
Hex Key	3/4
Installation Torque	275 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Screw Type Plated	Allen Y
Plating Type	Tin plated
Sub Brand	UNIVERSAL TERM
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810370261
UPC 12 Digit	7818103702611

## Dimensions

Dimension - Bolt Hole Size inch	0.31 in
Dimension - Bolt Size fraction	5/16
Dimension - D inch	0.94 in
Dimension - Height fraction	2 in
Dimension - Height inch	2.03 in
Dimension - Height mm	51.6 mm
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	3.00 in
Dimension - N inch	0.47 in

Dimension - Pad Width inch	1.02 in
Dimension - Screw Size inch	11/16
Dimension - Stud Size fraction	5/16
Dimension - Stud Size inch	5/16 in
Dimension - Thread Size	5/16 in
Dimension - Width inch	1.02 in
Dimension - Width mm	25 mm

## Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

## Conductor Related

Conductor - AL Str Size	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil
Conductor - AL Str Size Range	6 Str.- 300 Kcmil
Conductor - Copper Solid Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	4 AWG-4/0 AWG
Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil
Conductor - Copper Str Size Range	6 Str.- 300 Kcmil
Conductor Size	6 AWG-300 KCMIL
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> </ul>
Number of Conductors	2

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B

Standards - RoHS Compliance EX  
Status  
UL Listed Yes

**Logistics**

Carton Quantity 72

**Product Assets**

[3D Models - K11A30U\\_MODEL-IGES](#)

[3D Models - K11A30U\\_MODEL-PDF](#)  
[3D Models - K11A30U\\_MODEL-STEP](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_K22AU\\_Lineart](#)  
[Sales Drawings - se210997](#)  
[Specifications - K11A30U](#)



A Hubbell brand