

# K11A34U2, Two Conductor Two Hole Mounting Stacked Aluminum Panel Board Set Screw Connector

By Burndy  
Catalog # [K11A34U2](#)



Aluminum Universal Terminal, 2 Hole, Two: 4/0 AWG (Str)-500 kcmil, 1/4" Stud, .69" Stud Hole Spacing, 2 Screws, Al/Cu Rated, Tin Plated.

## Features

- Constructed from high strength, extruded aluminum alloy
- Electro tin-plated to provide low contact resistance

## Application

For Aluminum and Copper Conductors

## General

Catalog Number	K11A34U2
Connector Type	Stacked
EU RoHS Indicator	Yes
Hex Key	3/8
Installation Torque	375 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Screw Type Plated	Allen Y
Plating Type	Tin plated
Sub Brand	UNIVERSAL TERM
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810370278
UPC 12 Digit	7818103702788

## Dimensions

Dimension - Bolt Hole Size inch	0.25 in
Dimension - Bolt Size fraction	1/4
Dimension - D inch	2.31 in
Dimension - Height fraction	2.4 in
Dimension - Height inch	2.40 in
Dimension - Height mm	61 mm
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	74 mm
Dimension - Length Overall inch	2.91 in

Dimension - N inch	0.25 in
Dimension - Pad Width inch	1.45 in
Dimension - Screw Size inch	15/16
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4 in
Dimension - Width fraction	1-11/25 in
Dimension - Width inch	1.44 in
Dimension - Width mm	37 mm

## Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

## Conductor Related

Conductor - AL Str Size	4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil
Conductor - AL Str Size Range	4/0 AWG-500 kcmil
Conductor - Copper Solid Size	4/0 AWG
Conductor - Copper Solid Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	4/0 AWG-500 kcmil
Conductor Size	4/0 AWG-500 KCMIL
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> </ul>
Number of Conductors	2

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B

Standards - Industry Standards Met UL 486A-486B  
Standards - RoHS Compliance Status EX  
UL Listed Yes

**Logistics**

Pallet Quantity 90

**Product Assets**

Catalogs - BURNDY Master Catalog - Section A - Mechanical  
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog  
Customer Notices - Prop 65 Notice  
Interactive Catalog - BURNDY Full-Line Digital Catalog  
Product Cross Section Image(s) - BUR\_K22AU\_Lineart  
Sales Drawings - se210997  
Specifications - K11A34U2



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_MX-K11A34U2-SPEC-EN | REV 10/2024