



K12P6C3P1/OCAG1, AL Neutral Bar, #14-1/0 AWG, #14-6 AWG, 15 Circuits



By Burndy
Catalog # [K12P6C3P1/OCAG1](#)

Dual rated Aluminum Neutral bar for copper and aluminum conductors, 15 Circuits, 14-1/0 AWG , 14-6AWG wire range

General

Catalog Number	K12P6C3P1/OCAG1
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810659137
UPC 12 Digit	7818106591377

Dimensions

Dimension - Height inch	0.62 in
Dimension - L Length Overall mm	110 mm
Dimension - Length Overall inch	4.34 in
Dimension - Width inch	0.38 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size Range	(3) 14-1/0 AWG , (12) 14-6 AWG
Conductor - Copper Str Size Range	(3) 14-1/0 AWG , (12) 14-6 AWG
Number of Conductors	15

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Carton Quantity	150
-----------------	-----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50038331](#)
- [Specifications - BURNDY_K12P6C3P1OCAG1_Specsheet](#)