

## K21A36U2, AL Universal Terminal, 3 Conductor, 2 Hole, #2 AWG Str-600 kcmil, 3/8" Stud, 1.38" Spacing, 3 Screws

By Burndy  
Catalog # [K21A36U2](#)

Aluminum Universal Terminal, 2 Hole, Three: 2 AWG (Str)-600 kcmil, 3/8" Stud, 1.38" Stud Hole Spacing, 3 Screws, Al/Cu Rated, Tin Plated.

### Features

- Constructed from high strength, extruded aluminum alloy
- Electro tin-plated to provide low contact resistance

### Application

For Aluminum and Copper Conductors

### General

Catalog Number	K21A36U2
Connector Type	Stacked
EU RoHS Indicator	Yes
Installation Torque	375 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	3
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin plated
Sub Brand	UNIVERSAL TERM
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810370322
UPC 12 Digit	7818103703222

### Dimensions

Dimension - Bolt Hole Size inch	0.38 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	2.31 in
Dimension - Height fraction	3 in
Dimension - Height inch	3.03 in
Dimension - Height mm	77 mm
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	125 mm



Dimension - Length Overall inch	4.91 in
Dimension - N inch	0.38 in
Dimension - Pad Width inch	2.49 in
Dimension - Stud Size inch	3/8 in
Dimension - Width fraction	2-1/2 in
Dimension - Width inch	2.5 in
Dimension - Width mm	64 mm

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - AL Str Size	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - AL Str Size Range	2 Str. - 600 Kcmil
Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil
Conductor - Copper Str Size Range	2 Str. - 600 Kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> </ul>
Number of Conductors	3

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Product Assets

[3D Models - K21A36U2\\_MODEL-IGES](#)

[3D Models - K21A36U2\\_MODEL-STEP](#)  
[3D Models - K21A36U2\\_MODEL-PDF](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_K22AU\\_Lineart](#)  
[Sales Drawings - se210997](#)  
[Specifications - K21A36U2](#)



A Hubbell brand