

K22A39U2, AL Universal Term, 4 Conductor, 2-Hole, 1/0 AWG Str-750 kcmil, 3/8" Stud, 1.38" Spacing, 4 Screws, Al/Cu Rated

By Burndy
Catalog # [K22A39U2](#)

Aluminum Universal Terminal, 2 Hole, Four: 1/0 AWG (Str)-750 kcmil, 3/8" Stud, 1.38" Stud Hole Spacing, 4 Screws, Al/Cu Rated, Tin Plated.

Features

- Constructed from high strength, extruded aluminum alloy
- Electro tin-plated to provide low contact resistance

Application

For Aluminum and Copper Conductors

General

Catalog Number	K22A39U2
Connector Type	Stacked
EU RoHS Indicator	No
Installation Torque	375 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	4
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin plated
Sub Brand	UNIVERSAL TERM
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810370339
UPC 12 Digit	7818103703399

Dimensions

Dimension - Bolt Hole Size inch	0.38 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	2.31 in
Dimension - Height fraction	3 in
Dimension - Height inch	3.02 in
Dimension - Height mm	76.7 mm
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	125 mm



Dimension - Length Overall inch	4.91 in
Dimension - N inch	0.38 in
Dimension - Pad Width inch	2.86 in
Dimension - Stud Size inch	3/8 in
Dimension - Width fraction	3-3/50 in
Dimension - Width inch	2.86 in
Dimension - Width mm	78 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil
Conductor - AL Str Size Range	1/0-750 Acmil
Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil
Conductor - Copper Str Size Range	1/0-750 Acmil
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size
Number of Conductors	4

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B

Standards - Industry Standards UL 486A-486B
Met
Standards - RoHS Compliance NC
Status
UL Listed Yes

Product Assets

[3D Models - K22A39U2_MODEL-PDF](#)

[3D Models - K22A39U2_MODEL-IGES](#)
[3D Models - K22A39U2_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_K22AU_Lineart](#)
[Sales Drawings - se210997](#)
[Specifications - K22A39U2](#)



A Hubbell brand