

K2A29U, AL Universal Terminal, 2 Conductor, 1-Hole, #6 AWG Str-250 kcmil, 3/8" Stud, 2 Screws, Al/Cu Rated

By Burndy
Catalog # [K2A29U](#)

Aluminum Universal Terminal, 2 Conductor, 1 Hole, 6 AWG (Str)-250 kcmil, 3/8" Stud, 2 Screws, Al/Cu Rated, Tin Plated.

Features

- Constructed from high strength, extruded aluminum alloy
- Electro tin-plated to provide low contact resistance

Application

For Aluminum And Copper Conductors

General

Catalog Number	K2A29U
Connector Type	Parallel Set-Screw
EU RoHS Indicator	No
Hardware Type	3/8 UNC Slotted Set Screw
Installation Torque	275 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Tin plated
Sub Brand	UNIVERSAL TERM
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810600108
UPC 12 Digit	7818106001088

Dimensions

Dimension - Bolt Hole Size inch	0.38 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.50 in
Dimension - Height fraction	1.2 in
Dimension - Height inch	1.20 in
Dimension - Height mm	30.5 mm
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.56 in



Dimension - N inch	0.5 in
Dimension - Pad Width inch	1.66 in
Dimension - Screw Size inch	3/8
Dimension - Stud Size inch	3/8 in
Dimension - Width fraction	1-33/50 in
Dimension - Width inch	1.66 in
Dimension - Width mm	42 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - AL Str Size Range	6 Str.- 250 Kcmil
Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	6 Str.- 250 Kcmil
Conductor Size	6 AWG-250 KCMIL
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size
Number of Conductors	2

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	144
-----------------	-----

Product Assets

[3D Models - K2A29U_MODEL-STEP](#)

[3D Models - K2A29U_MODEL-PDF](#)

[3D Models - K2A29U_MODEL-IGES](#)

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_K2AU_Lineart](#)

[Sales Drawings - se210997](#)

[Specifications - K2A29U](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-K2A29U-SPEC-EN | REV 10/2024